

RM 90

Watch cleaning machine



Picture RM 90

Elma Order Nos

RM 90 - 230V	328 000 0000
RM 90 - 115V	328 000 1000
Basket inserts for disassembled movements of watches	300 010 1101

The universal watch cleaning machine for cleaning and drying

Fully automated watch cleaning machine for the cleaning of disassembled and assembled watch works. Two perfected cleaning systems are combined in one machine: The cleaning of assembled movements of watches by means of a watch work support and the cleaning of disassembled movements of watches in a perforated basket.

The universal watch cleaning machine for cleaning and drying Automatic watch cleaning machine for the cleaning of assembled and disassembled watch works Two perfected cleaning systems have been combined in one machine: cleaning of assembled watch works in the watch work holder, and cleaning of disassembled watch works in a wire basket. The cleaning intensity is adjusted to the individual cleaning parts by electronically controlled impulse periods. The watch work holder (included in the delivery volume) can hold up to six assembled watch works. It cleans highly efficiently by agitating the fastened watch works quickly in the liquid; the cleaning effect is caused by the reverse current created which can be adjusted steplessly via separate control. As the watch works are fastened to the watch work holder in vertical position, the pivots are additionally agitated inside their bearings (with relaxed main springs) which improves the cleaning effect.

Further product features

- automatic cleaning and drying of up to 6 watch works
- 2 perfected cleaning systems (rotation / vibration) combined in one machine
- stepless speed regulation
- corresponds with all valid safety regulations
- very easy to operate
- movement holder for 6 movements (included in delivery)
- 3 jars (included in delivery)

Technical Data

Outer dimensions of unit w/d/h (mm/ inch)	350 / 350 / 640 / 13 4/5 x 13 4/5 x 25 1/5
Weight (kg / lbs)	27.6 / 60.9

Technical and optical information are subject to change

Distributed by:

BIRKENSTOCK & CO. GMBH · D-21500 Geesthacht · Germany · ☎ +49 (0) 41 52 / 80 96 80 · 📠 +49 (0) 41 52 / 80 96 96 · www.beco-professionals.com

Anderungen, Verfügbarkeit und Preise der Produkte vorbehalten. Es gelten unsere Allgemeinen Geschäftsbedingungen, u.a. nachzulesen unter <http://www.beco-professionals.com>. Bitte informieren Sie uns, wenn Sie unsere Werbung nicht mehr erhalten möchten.

Technical changes as well as changes in production and prices are subject to our approval. For our terms of delivery and payment please go to <http://www.beco-professionals.com>. Please let us know if you don't want to receive our promotion anymore.

Sitz der Gesellschaft/Reg. office: D-21500 Geesthacht · Amtsgericht/Register Court: Lübeck HRB 314 GE · Geschäftsführer/Managing Directors: Jürgen Birkenstock, Marek Birkenstock · USt.Id.Nr./ VAT-Number: DE 135283788 · ILN 40 22739 00000 3 · WEEE.Reg.Nr.: DE12990100